



## FITone PROGRESSIVE

### 75MM POLYCARBONATE SEMI-FINISHED PROGRESSIVE LENS

Lens Diameter	Nom. Base (1.530)	Sag at 50mm	Sag at 40mm	Front Radius (mm)	True Curve (1.530)	RX True Curve (1.530)	RX True Curve (1.586)	Male Insert Gasket (mm)	Center Thickness (mm)	Edge Thickness (mm)	Back Curve (1.530)	Back Radius (mm)	ADD POWER	Design and Suggested Rx Range
Reality Used Size: 75mm	2.75	1.73±0.03	1.12±0.03	182.75	2.75±0.05	2.90±0.05	3.21±0.05	8.5mm	10.6±0.4	12.5±0.4	4.25	124.70	+1.00 to +3.00	-7.50 to -1.75
	4.75	2.85±0.03	1.84±0.03	110.19	4.75±0.05	4.81±0.05	5.32±0.05	10.5mm	12.5±0.4	10.5±0.4	4.25	124.70	+1.00 to +3.00	-1.50 to +3.00
	6.75	3.98±0.03	2.55±0.03	75.700	6.75±0.05	7.0±0.05	7.74±0.05	13mm	9.5±0.3	8.1±0.4	6.25	84.80	+1.00 to +3.00	+3.25 to +7.75