



# TECHNICAL BULLETIN

## DAC WHITE POLISH PAD

---

PRODUCT: PDR7300N DAC White

---

**PRIMARY USE:**

Polish pad for CR39/Hi Index lenses during ophthalmic manufacturing.

---

**DESCRIPTION:**

3" 7 leaf DAC White polishing pad. Back side of pad is laminated with low tack rubber based pressure sensitive adhesive for firm, temporary positioning onto bare lap tool.

---

**LINER:**

Bleached, densified kraft paper, clay filled with silicone on one side.

---

Recommended Times and Pressure:

LOH	4 - 5 minutes @ 0.3 to 0.4 bar
Coburn / Optek	4 - 5 minutes @ 16-18 psi

---

**TYPICAL PHYSICAL PROPERTIES:**

- Thickness:**  
Pad Material & Adhesive..... .024 " / .61mm (+/-0.003")  
Liner..... 4.8 mils (+/-0.2 mils)
  - Peel Adhesion:**  
PSTC #3  
Linered side..... 80 oz. (+/-5 oz)
  - Dynamic Shear:**  
(@ 12"/Min.)  
Linered side..... 45 lbs/in. (+/-6 lbs)
- 

**PACKAGING:**

250 per roll with plastic shrink wrap. Labeled in core with lot number information

---

No warranties are made in this Bulletin. All information, recommendations and descriptive material concerning DAC products are based upon research which is believed to be reliable but shall not constitute a warranty. Accordingly, all DAC products are sold with the understanding that purchaser will be solely responsible for determining the suitability of the materials for any purpose.